



Anchor, Tough One, 14in, 15,000 ft-lb rating, 2.5in hub, 1in threads

By Chance
Catalog # C1025003

Tough One Anchor Helix, 15,000 Ft Lbs (20,340 N-M), 14" (355 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

Features

- Installed with Chance anchor wrench C3031064 or C3030983
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

Application

Helical Anchoring

General

Catalog Number	C1025003
Coating	Painted
Number of Helices	1
Torque Rating	15000 ft-lbs
Type	Anchor Helix
UPC	096359008620

Dimensions

Anchor Helix Diameter(s)	14 in
Anchor Hub Size	2.5 in
Dimensions	13.500 in x 13.500 in x 7.500 in
Height	7.5 in
Length	13.5 in
Rod Diameter	<ul style="list-style-type: none">• 0.75• 1 in

Weight	31.487 lb
Width	13.5 in

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
--------------------------	--

Logistics

Pallet Quantity	48
Standard Package	2

Product Assets

- Catalogs - Anchor Tools
- Catalogs - Anchors
- Catalogs - Dependable Anchoring Solutions
- Catalogs - Communications Catalog
- Installation Manuals - TOUGH ONE® Anchors
- Installation Manuals - Holding Capacity Chart - PISA Anchors
- Installation Manuals - Holding Capacity Chart - Soil Classification
- Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide
- Literature - CHANCE Anchor Tool Inspection and Maintenance
- Literature - How to Match Anchors and Installing Wrenches
- Sales Drawings - Tough One 10,000 & 15,000
- Specifications - C1025003
- Video - CHANCE Pisa Drive Tools
- Video - CHANCE Tough One and PISA Anchor Installation



A Hubbell brand