



Anchor, Tough One, 12in, 10,000 ft-lb rating, 2.5in hub, 1in threads

By Chance
Catalog # [C1025006](#)

Tough One Anchor Helix, 10,000 Ft Lbs (10,848 N-M), 12" (304 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.



*Representative Image

Features

- Installed with Chance anchor wrench C3031064 or C3030983
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

General

Application	Helical Anchoring
Catalog Number	C1025006
Coating	Painted
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359008699

Dimensions

Anchor Helix Diameter(s)	12 in
Anchor Hub Size	2.5 in
Dimensions	12.000 in x 12.000 in x 7.500 in
Height	7.5 in
Length	12 in
Rod Diameter	0.75
	1 in
Weight	21.227 lb
Width	12 in

Logistics

Pallet Quantity	72
Standard Package	2

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06130E_Tough_One_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Tough One 10,000 & 15,000](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C1025006-SPEC-EN | REV 6/2024