



# Anchor, Tough One, 10in, 10,000 ft-lb rating, 2.5in hub, 5/8in threads

By Chance  
Catalog # [C1025009](#)

Tough One Anchor Helix, 10,000 Ft Lbs (10,848 N-M), 10" (254 mm) Helix for use with 0.625" (15.9 mm) Rod.

## Features

- Installed with Chance anchor wrench C3031064 or C3030983
- The anchor’s sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 5/8" threads to fit 5/8" diameter Pisa rod
- Anchors are painted with a black paint

## Application

Helical Anchoring

## General

Catalog Number	C1025009
Coating	Painted
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359008743

## Dimensions

Anchor Helix Diameter(s)	10 in
Anchor Hub Size	2.5 in
Rod Diameter	0.625 in
Weight	13.779 lb



\*Representative Image

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

## Logistics

Pallet Quantity	144
Standard Package	4

## Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - TOUGH ONE® Anchors](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Sales Drawings - Tough One 10,000 & 15,000](#)
- [Specifications - C1025009](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand