



Anchor, Tough One, 12in, 10,000 ft-lb rating, 2.25in, 1in threads

By Chance
Catalog # [C1025202](#)

Tough One Anchor Helix, 10,000 Ft Lbs (13,558 N-M), 12" (304 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

Features

- Installed with Chance anchor wrench C1021583
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

Application

Helical Anchoring

General

Catalog Number	C1025202
Coating	Painted
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359008798

Dimensions

Anchor Helix Diameter(s)	12 in
Anchor Hub Size	2.25 in
Dimensions	11.500 in x 11.500 in x 7.250 in
Height	7.25 in
Length	11.5 in
Rod Diameter	<ul style="list-style-type: none">• 0.75• 1 in
Weight	21.54 lb

Width 11.5 in

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2025)
--------------------------	--

Logistics

Pallet Quantity	72
Standard Package	2

Product Assets

- [360 Product View - CHAN_C1025201](#)
- [3D Product View - CHAN_C1025201](#)
- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - TOUGH ONE® Anchors](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Sales Drawings - Tough One 2-1/4 10,000](#)
- [Specifications - C1025202](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand