



Anchor, Tough One, 14in, 10,000 ft-lb rating, 2.25in, 1in threads

By Chance
Catalog # [C1025203](#)

Tough One Anchor Helix, 10,000 Ft Lbs (13,558 N-M), 14" (355 mm) Helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.



Features

- Installed with Chance anchor wrench C1021583
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

General

Application	Helical Anchoring
Catalog Number	C1025203
Coating	Painted
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359008804

Dimensions

Anchor Helix Diameter(s)	14 in
Anchor Hub Size	2.25 in
Dimensions	14.000 in x 14.000 in x 7.000 in
Height	7 in
Length	14 in
Rod Diameter	0.75
	1 in
Weight	25.5 lb
Width	14 in

Logistics

Pallet Quantity	48
Standard Package	2

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06130E_Tough_One_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Tough One 2-1/4 10,000](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C1025203-SPEC-EN | REV 6/2024