



Anchor, Tough One, 12in, 10,000 ft-lb rating, 2.25in hub, 5/8in threads

By Chance
Catalog # [C1025210](#)



Tough One Anchor Helix, 10,000 Ft Lbs (10,848 N-M), 12" (304 mm) Helix for use with 0.625" (15.9 mm) Rod.

Features

- Installed with Chance anchor wrench C1021583
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 5/8" threads to fit 5/8" diameter Pisa rod
- Anchors are painted with a black paint

General

Application	Helical Anchoring
Coating	Painted
EU RoHS Indicator	No
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359008880

Dimensions

Anchor Helix Diameter(s)	12 in
Anchor Hub Size	2.25 in
Rod Diameter	0.625 in
Weight	20.79 lb

Certifications And Compliance

RUS Listed Reference	z - Anchors, Power-Installed Screw, Distribution
----------------------	--

Logistics

Pallet Quantity	72
Standard Package	2

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06130E_Tough_One_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Tough One 2-1/4 10,000](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C1025210-SPEC-EN | REV 6/2024