



1.75" Square Shaft Lead (SS175), 8/10/12/14 x 10ft

By CHANCE Utility
Catalog # C1100247

SS175, 120" long with 8",10",12",14" helices



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Finish Type	Galvanized
Number of Helices	4
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb.
Torque Rating	10500 ft-lbs
Type	Lead Sections
UPC	096359009719

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in - 14 in
Dimensions	120.00 in x 14.000 in x 14.000 in
Height	14.000 in
Length	120.00 in
Weight	146.020 lb
Width	14.000 in

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - Anchors (4)
- Installation Manuals - TD06132E_Type_SS_and_RR_Anchors
- Installation Manuals - Holding Capacity Chart - Soil Classification
- Installation Manuals - Holding Capacity Chart - SS175 Anchors
- Literature - CHANCE® Building Code Evaluated Products December 2022
- Literature - Square Shaft Efficient Helical Pile Design (BR04326E)
- Literature - New Construction Helical Pile Foundation System (SF04215E_0419)
- Literature - CHANCE Anchor Tool Inspection and Maintenance (TD06031E)
- Literature - Anchoring (CA12002E)
- Sales Drawings - SS175 Anchors (SA11010018)
- SDS - MSDS - Galvanized Steel Products
- Test Documents - ICC Evaluation (NER2794)
- Video - CHANCE Square Shaft Anchor Tools Selection Process (VI0651E)
- Video - CHANCE Square Shaft Anchor Installation (VI0655E)

Related Products

- C1100140 - Anchor, Extension, SS175, X 10ft
- C1100138 - Anchor, Extension, SS175, X 7ft
- C1100136 - Anchor, Extension, SS175, X 3.5ft
- C1100137 - Anchor, Extension, SS175, X 5ft



A proud member of the Hubbell Family.