



1.5" Square Shaft Helical Extension (SS 150), 14/14/14 x 10ft

By CHANCE Utility
Catalog # C1100475

SS150, 123" long with 14",14",14" helices.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	7000 ft-lbs
Type	Anchor Extensions
UPC	096359009825

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Length	120.00 in
Weight	138.837 lb

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [P0010041P - Square Shaft \(SS5/SS150\) Hardware](#)
- [O55449P - Square Shaft \(SS5/SS150\) Nut](#)



A proud member of the Hubbell Family.