



Shackle, Anchor SS200

By CHANCE Utility
Catalog # [C1100557](#)

SS200 Chain Shackle



Features

- Specifically designed to be used with SS200 anchors
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Type	Shackles
UPC	096359009900

Dimensions

Dimensions	8.25 in x 6.625 in x 3.250 in
Height	3.250 in
Length	8.25 in
Weight	11.760 lb
Width	6.625 in

Logistics

Pallet Quantity	160
Standard Package	4

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS200 Anchors \(SA11010019\)](#)
- [Sales Drawings - Shackle SS175, SS200, SS225 \(SA1100134\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Technical Solutions - CH-C1100557-SPEC-EN](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)



A proud member of the Hubbell Family.