



Shackle, Anchor SS225

By CHANCE Utility
Catalog # [C1100558](#)

SS225 Chain Shackle.



Features

- Specifically designed to be used with SS225 anchors
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	200000 lb.
Type	Shackles
UPC	096359009917

Dimensions

Dimensions	9.50 in x 8.000 in x 4.000 in
Height	4.000 in
Length	9.50 in
Weight	14.700 lb
Width	8.000 in

Logistics

Pallet Quantity	128
Standard Package	4

Product Assets

[Catalogs - Anchors \(4\)](#)
[Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
[Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
[Literature - Anchoring \(CA12002E\)](#)
[Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
[Sales Drawings - Shackle SS175, SS200, SS225 \(SA1100134\)](#)
[SDS - MSDS - Galvanized Steel Products](#)
[Technical Solutions - CH-C1100558-SPEC-EN](#)
[Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
[Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C1100558-SPEC-EN | REV 1/2024