



2" Square Shaft Extension (SS200), 7ft

By CHANCE Utility
Catalog # [C1100565](#)

SS200, Extension 7'



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Finish Type	Galvanized
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359009948

Dimensions

Dimensions	84.00 in x 3.250 in x 5.250 in
Height	5.250 in
Length	84.00 in
Weight	98.000 lb
Width	3.250 in

Logistics

Pallet Quantity	12
Standard Package	1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS200 Anchors \(SA11010019\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Technical Solutions - CH-C1100565-SPEC-EN](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [P0011445P](#)
- [P0010030P - Square Shaft \(SS200\) Nut Replacement](#)



A proud member of the Hubbell Family.