



## 2" Square Shaft Lead (SS200), 14/14/14 x 10ft

By CHANCE Utility  
Catalog # [C1100572](#)

SS200, 120" long with 14",14",14" helices.



\*Representative Image

### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

### Application

Helical Anchoring

### General

Coating	Galvanized
EU RoHS Indicator	No
Finish Type	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Lead Sections
UPC	096359009993

### Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Dimensions	120.00 in x 14.00 in x 14.00 in
Height	14.00 in
Length	120.00 in
Weight	228.000 lb
Width	14.00 in

### Logistics

Pallet Quantity	12
Standard Package	1

### Product Assets

- Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure (BR04146E)
- Catalogs - Anchors (4)
- Installation Manuals - TD06132E\_Type\_SS\_and\_RR\_Anchors
- Installation Manuals - Holding Capacity Chart - Soil Classification
- Installation Manuals - Holding Capacity Chart - SS200 Anchors
- Literature - Square Shaft Efficient Helical Pile Design (BR04326E)
- Literature - New Construction Helical Pile Foundation System (SF04215E\_0419)
- Literature - CHANCE Anchor Tool Inspection and Maintenance (TD06031E)
- Literature - Anchoring (CA12002E)
- Sales Drawings - SS200 Anchors (SA11010019)
- SDS - MSDS - Galvanized Steel Products
- Video - CHANCE Square Shaft Anchor Tools Selection Process (VI0651E)
- Video - CHANCE Square Shaft Anchor Installation (VI0655E)

### Related Products

- [C1100565 - 2" Square Shaft Extension \(SS200\), 7ft](#)
- [C1100563 - 2" Square Shaft Extension \(SS200\), 3.5ft](#)
- [C1100566 - 2" Square Shaft Extension \(SS200\), 10ft](#)
- [C1100564 - 2" Square Shaft Extension \(SS200\), 5ft](#)



A proud member of the Hubbell Family.