



## 2" Square Shaft Helical Extension (SS200), 14 x 4ft

By CHANCE Utility  
Catalog # [C1100577](#)

SS200, 4' long (1219 mm) with 14" helix



### Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

### Application

Helical Anchoring

### General

Coating	Galvanized
Finish Type	Galvanized
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359010029

### Dimensions

Anchor Helix Diameter(s)	14 in
Dimensions	48.00 in x 14.000 in x 14.000 in
Height	14.000 in
Length	48.00 in
Weight	76.440 lb
Width	14.000 in

### Logistics

Pallet Quantity	12
Standard Package	1

### Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E\\_Type\\_SS\\_and\\_RR\\_Anchors Literature - New Construction Helical Pile Foundation System \(SF04215E\\_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS200 Anchors \(SA11010019\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

### Related Products

- [PO011445P](#)
- [PO010030P - Square Shaft \(SS200\) Nut Replacement](#)



A proud member of the Hubbell Family.