



2" Square Shaft Helical Extension (SS200), 14/14/14 x 10ft

By CHANCE Utility
Catalog # [C1100586](#)

SS200, 124" long with 14", 14", 14" helices.



Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation

Application

Helical Anchoring

General

Coating	Galvanized
Finish Type	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	16000 ft-lbs
Type	Anchor Extensions
UPC	096359512943

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in - 14 in
Dimensions	120.00 in x 14.00 in x 14.00 in
Height	14.00 in
Length	120.00 in
Weight	224.900 lb
Width	14.00 in

Logistics

Standard Package 1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS200 Anchors \(SA11010019\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [P0011445P](#)
- [P0010030P - Square Shaft \(SS200\) Nut Replacement](#)



A proud member of the Hubbell Family.