



2.25" Square Shaft Helical Extension (SS225), 14/14 x 7ft

By CHANCE Utility
Catalog # [C1100652](#)

SS225, 78" long with 14", 14" helices.



*Representative Image

Features

- Finish: Galvanized
- Capacity of helical pile can be determined by measuring installation
- Bolt and nut are assembled to extension at the factory

Application

Helical Anchoring

General

Coating	Galvanized
EU RoHS Indicator	No
Finish Type	Galvanized
Number of Helices	2
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	200000 lb.
Torque Rating	21000 ft-lbs
Type	Anchor Extensions
UPC	096359010111

Dimensions

Anchor Helix Diameter(s)	14 in - 14 in
Dimensions	84.00 in x 14.00 in x 14.00 in
Height	14.00 in
Length	84.00 in
Width	14.00 in

Logistics

Standard Package 1

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - Square Shaft Efficient Helical Pile Design \(BR04326E\)](#)
- [Sales Drawings - SS225 Anchors And Extensions \(SA11010020\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Technical Solutions - CH-C1100652-SPEC-EN](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

- [056292P - Square Shaft \(SS225\) Nut Replacement](#)
- [P0011771P](#)



A proud member of the Hubbell Family.