



Helical Pulldown Micropile, Anchor, SS5, 8/10/12in X 7ft

By Chance
Catalog # [C1100921](#)



Helical Pulldown® Micropile Square Shaft (SS 5) Lead Section, 5' 6" (1676 mm) long with 8" (203 mm) - 10" (254 mm) -12" (304 mm) Helices.

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Catalog Number	C1100921
Coating	Galvanized, ASTM A-153
Number of Helices	3
Pipe Type	Square Bar
Style	Helical Pulldown® Micropile
Torque Rating	5500 ft-lbs
Type	HPDM Plates

Dimensions

Anchor Helix Diameter(s)	8 in - 10 in - 12 in
Foundation Diameter	1.5 in
Foundation Length	84 in
Length	84 in
Weight	65.856 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Foundations & Installing Tools for Transmission & Substations](#)
- [Installation Manuals - Holding Capacity Chart - SS5 Anchors](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Sales Drawings - Helical Pulldown Micropile](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - C1100921](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - Grouted Micropile for Increased Capacity](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand