



LEAD, SS200, 10/12/14 X 7FT

By Chance
Catalog # [C1100924](#)

Square Shaft (SS 200) Lead Section 7' (2134 mm) long with 10" (254 mm) -12" (304 mm) - 14" (355 mm) Helices.

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Catalog Number	C1100924
Coating	Galvanized
Number of Helices	3
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	150000 lb.
Torque Rating	15000 ft-lbs
Type	Lead Sections
UPC	096359721765



Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in
Length	84 in

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification Literature - New Construction Helical Pile Foundation System](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - Model Specifications - Atlas 2-Piece Systems, Rev 040207 \(230881\)](#)
- [Specifications - Model Specifications - Helical Pulldown Micropile 01-1206, Rev 2018](#)
- [Specifications - Model Specifications - Atlas 2-Piece Systems with Lateral, Rev 040207](#)
- [Specifications - Model Specifications - Helical Tieback 31-0503, Rev 081514](#)
- [Specifications - Model Specifications - Helical Pile Foundations 01-0303, Rev 102020](#)