



Anchor, Lead, SS150, 10/12/14/14 X 10ft

By Chance
Catalog # [C1101052](#)

Square Shaft (SS 150) Lead Section, 10' (3048 mm) long with 10" (254 mm) -12" (304 mm) -14" (355 mm) -14" (355 mm) Helices.



Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

General

Application	Helical Anchoring
Coating	Galvanized, ASTM A-153
Number of Helices	4
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	7000 ft-lbs
Type	Lead Sections
UPC	096359566519

Dimensions

Anchor Helix Diameter(s)	10 in - 12 in - 14 in - 14 in
Length	120 in
Weight	135.917 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Anchoring](#)
- [Literature - New Construction Helical Pile Foundation System](#)
- [Sales Drawings - SS150 Anchors](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)



A Hubbell brand