



Anchor, Swamp, SS5, 10in X 8ft Thimbleye

By Chance
Catalog # C1101169

Swamp Anchor (SS 5) Lead Section, 8' (2438 mm) long with 10" (254 mm) Helices and Thimbleye adapter attached.

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Catalog Number	C1101169
Coating	Galvanized, ASTM A-153
Eyenut Style	Thimbleye
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.



Torque Rating	5500 ft-lbs
Type	Lead Sections
UPC	096359646112

Dimensions

Anchor Helix Diameter(s)	10 in
Length	96 in
Weight	46 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- Catalogs - Anchor Tools
- Catalogs - Anchors
- Installation Manuals - Holding Capacity Chart - SS5 Anchors
- Installation Manuals - TD06132E_Type_SS_and_RR_Anchors
- Installation Manuals - Holding Capacity Chart - Soil Classification
- Literature - CHANCE Anchor Tool Inspection and Maintenance
- Sales Drawings - SS5 RUS Swamp Anchor
- Specifications - C1101169
- Video - CHANCE Square Shaft Anchor Installation
- Video - Chance Foundation Solutions Anchor/Pile Installation Tools
- Video - CHANCE Square Shaft Anchor Tools Selection Process



A Hubbell brand