



Anchor, Swamp, SS5, 15in X 8ft Thimbleye

By CHANCE Utility
Catalog # [C1101171](#)

Swamp Anchor (SS 5) Lead Section, 8' (2438 mm) long with 15" (381 mm) Helices and Thimbleye adapter attached.



*Representative Image

Features

- Square Shaft Lead Sections are assembled to Square Shaft Extension with through bolt.
- The helical shaped plates do not auger into the soil but rather screw into it with minimal soil disturbance
- Hot dipped galvanized per ASTM A153
- Capacity of anchor can be determined by measuring installation torque

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Eye Nut Style	Thimbleye
Number of Helices	1
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	70000 lb.
Torque Rating	5500 ft-lbs
Type	Lead Sections
UPC	096359619277

Dimensions

Anchor Helix Diameter(s)	15 in
Length	96.000 in
Weight	81 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Brochures - CHANCE® Foundation Solutions Helical Deep Foundation Products Brochure \(BR04146E\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - New Construction Helical Pile Foundation System \(SF04215E_0419\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Sales Drawings - SS5 RUS Swamp Anchor \(SA1101169\)](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)



A proud member of the Hubbell Family.