



TRANSFORMER BRACKET, 3- POSITION, ALUMINUM RACK STYLE with NEMA A and B LUG SPACING

By Chance
Catalog # [C12MW30A](#)

Bracket, Transformer

Features

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 2,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 1,550 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 1,275 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 1,075 lbs. maximum recommended per phase for 3 simultaneous loads

General



Catalog Number	C12MW30A
Type	Bolted Pole Mount Bracket
UPC	096359579434

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Sales Drawings - Wing Cluster Mount Sales Drawing](#)
[Specifications - C12MW30A](#)



A Hubbell brand