



**TRANSFORMER BRACKET, 3-  
POSITION, ALUMINUM BANDED  
STYLE w/NEMA A, B and C LUG  
SPACING for 9-1/2in to 19-1/2in  
DIA. POLES**

By Chance  
Catalog # [C15M391436CES](#)



Aluminum, banded style transformer bracket for mounting 3 transformers with NEMA A, B or C lug spacing. Includes six 5/8" x 2-1/2" square head machine bolts and nuts for type A, B or C transformer lugs. Packaged in weatherproof bag for outside storage.

**Features**

- Lightweight 6061-T6 aluminum
- Recommend maximum load ratings based on distance from bracket face to center of gravity of the installed equipment
- 14" = 4,000 lbs. maximum recommended per phase for 3 simultaneous loads
- 18" = 3,100 lbs. maximum recommended per phase for 3 simultaneous loads
- 22" = 2,550 lbs. maximum recommended per phase for 3 simultaneous loads
- 26" = 2,100 lbs. maximum recommended per phase for 3 simultaneous loads
- For replacement bolts order six each P2160185P or one kit of six bolts, catalog number PSC2160587

**General**

Catalog Number                      C15M391436CES

Type                                      Banded Pole Mount Bracket  
UPC                                        096359583547

**Certifications And Compliance**

Buy America(n) Qualified              TAA Compliant (All status valid  
till December 2024)

**Logistics**

Pallet Quantity                              4

**Product Assets**

- [Installation Manuals - Banded Aluminum Cluster Mount](#)
- [Installation Instructions](#)
- [Sales Drawings - Mount, Jumbo Cluster](#)
- [Specifications - C15M391436CES](#)
- [Video - CHANCE Banded Transformer Bracket](#)