



PLASTIC LASHING STRAP, 16in

By CHANCE Utility
Catalog # [C16PLLC](#)

Lashing straps used in conjunction with spacers to secure communications cable to messenger strand.



Features

- Includes integral buckle for securing
- Loop strength 250 lbs.
- Black acetal with stainless steel locking barbs in buckle
- UV resistant and halogen free
- Use PSC2170130 strap tensioning tool for tensioning and cutting excess strap material

General

Material Plastic
UPC 096359657071

Dimensions

Length 16 in
Weight 0.03 lb
Width 0.5 in

Logistics

Carton Quantity 500
Pallet Quantity 12000

Product Assets

[Sales Drawings - SAC10PLLC](#)
[Video - Hubbell® Messenger Installation \(VI012006E\)](#)

Related Products

[PSC2170130 - TENSIONING TOOL for PLASTIC LASHING STRAPS](#)
[CDLC - Lashing Wire Clamp, Type D, 1/4in to 7/16in Strand Size](#)
[PSC2080426 - STACKABLE SPACER](#)
[PSC2080421 - BELL SPACER CABLE, 1/2in](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C16PLLC-SPEC-EN | REV 1/2024