



**DISCONTINUED - Anchor, PISA 4,
10in, 1in threads bevel leading edge**

By Chance
Catalog # [C199020104](#)

DISCONTINUED - Standard Strength Anchor Helix.; 4,000 Ft Lbs (5,424 N-M), 10" (254 mm) beveled leading edge helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

Features

- Replaced by PSC1022455
- Installed with Chance anchor wrench C1021583
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

Application

Helical Anchoring

General

Catalog Number	C199020104
Coating	Painted
Number of Helices	1
Torque Rating	4000 ft-lbs
Type	Anchor Helix
UPC	096359234937

Dimensions

Anchor Helix Diameter(s)	10 in
Anchor Hub Size	1.375 in
Dimensions	9.500 in x 9.000 in x 9.000 in
Height	9 in
Length	9.5 in
Rod Diameter	<ul style="list-style-type: none">• 0.75• 1 in

Weight	12.544 lb
Width	9 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	-----------------------------------------------------

Logistics

Pallet Quantity	144
Standard Package	4

Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - TD06131E_PISA_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Literature - Power Installed Screw Anchor Offering](#)
- [Sales Drawings - PISA 4 1-3/8 Core, Sharpened](#)
- [Specifications - C199020104](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)