



# Anchor, PISA 7, 2-10in, 1in threads bevel leading edge

By Chance  
Catalog # [C199020117](#)

Pisa 7 Anchor Helix; 7,000 Ft Lbs ( 9,492 N-M), Two 10" (254 mm) beveled leading edge helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

## Features

- Installed with Chance anchor wrench C3031064 or C3030983
- Anchor has curvilinear leading edges to help penetrate rocky soils and to reduce damage during installation
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

## Application

Helical Anchoring

## General

Catalog Number	C199020117
Coating	Painted
Number of Helices	2
Torque Rating	7000 ft-lbs
Type	Anchor Helix
UPC	096359593676

## Dimensions

Anchor Helix Diameter(s)	10 in - 10 in
Anchor Hub Size	1.5 in
Dimensions	32.000 in x 10.000 in x 10.000 in
Height	10 in
Length	32 in
Rod Diameter	<ul style="list-style-type: none"><li>• 0.75</li></ul>



\*Representative Image

Weight	<ul style="list-style-type: none"><li>• 1 in</li></ul> 22.863 lb
Width	10 in

## Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2024)
--------------------------	------------------------------------------------------

## Logistics

Pallet Quantity	30
Standard Package	1

## Product Assets

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - TD06131E\\_PISA\\_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Sales Drawings - PISA 7 1-1/2 Core, Sharpened](#)
- [Specifications - C199020117](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)



A Hubbell brand