



# Anchor, Disk Rod, 3/4in X 8ft Thimbleye

By Chance  
Catalog # [C2000049AW](#)

Corrosion-Resistant Disk Anchor Protected Rod 0.75" (19.1 mm) Diameter Rod, 8' (2438 mm) long with Thimbleye. Cap Nut and fiber washer is attached.



## Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

## General

Application	Earth Tension Anchoring
Coating	Galvanized, ASTM A-153, Black Paint, Plastic Tube
Eyenuit Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	23000 lb.
Type	Corrosion-Resistant Anchor Parts
UPC	096359614784

## Dimensions

Length	96 in
Rod Diameter	0.75 in
Weight	0.22 lb

## Logistics

Standard Package 1

## Product Assets

- [Catalogs - Appendix A - Transmission And Substation Technical Design Manual](#)
- [Installation Manuals - TD06134E\\_Corrosion\\_Protected\\_Disk\\_Anchors](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Threaded Thimbleye Rod 3/4"](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
CH-C2000049AW-SPEC-EN | REV 6/2024