



Anchor, Disk Rod, 1in X 10ft Thimbleye

By CHANCE Utility
Catalog # [C2000052AW](#)

Corrosion-Resistant Disk Anchor Protected Rod 1" (25.4 mm) Diameter Rod, 10' (3048 mm) long with Thimbleye. Cap Nut and fiber washer is attached.



*Representative Image

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

Application

Earth Tension Anchoring

General

Coating	Galvanized, ASTM A-153, Black Paint, Plastic Tube
Eyenuit Style	Thimbleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	36000 lb.
Type	Corrosion-Resistant Anchor Parts
UPC	096359614746

Dimensions

Length	120.000 in
Rod Diameter	1.000 in
Weight	16.250 lb

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Appendix A - Transmission And Substation Technical Design Manual \(TD_06_088_E\)](#)
- [Installation Manuals - TD06134E_Corrosion_Protected_Disk_Anchors](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Threaded, Thimbleye Rod, 1" \(SA2000051AW\)](#)



A proud member of the Hubbell Family.