



Anchor, Disk Rod, 3/4in X 8ft Twineye

By Chance
Catalog # [C2000055AW](#)

Corrosion-Resistant Disk Anchor Protected Rod 0.75" (19.1 mm) Diameter Rod, 8' (2438 mm) long with Twineye. Cap Nut and fiber washer is attached.



*Representative Image

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

General

| | |
|------------------|--|
| Application | Earth Tension Anchoring |
| Catalog Number | C2000055AW |
| Coating | Galvanized, ASTM A-153, Black Paint, Plastic Tube |
| EyenuT Style | Twineye |
| Strength Note | Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. |
| Tensile Strength | 23000 lb. |
| Type | Corrosion-Resistant Anchor Parts |
| UPC | 096359614791 |

Dimensions

| | |
|--------------|---------------------------------|
| Dimensions | 96.000 in x 3.500 in x 3.500 in |
| Height | 3.5 in |
| Length | 96 in |
| Rod Diameter | 0.75 in |
| Weight | 16.52 lb |
| Width | 3.5 in |

Logistics

Standard Package 1

Product Assets

- [Catalogs - Appendix A - Transmission And Substation Technical Design Manual](#)
- [Installation Manuals - TD06134E_Corrosion_Protected_Disk_Anchors](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Threaded Twineye Rod 3/4"](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C2000055AW-SPEC-EN | REV 6/2024