



Anchor, Disk Rod, 1in X 9ft Twineye

By Chance

Catalog # [C2000058AW](#)

Corrosion-Resistant Disk Anchor Protected Rod 1" (25.4 mm) Diameter Rod, 9' (2743 mm) long with Twineye. Cap Nut and fiber washer is attached.



*Representative Image

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

General

Application	Earth Tension Anchoring
Coating	Galvanized, ASTM A-153, Black Paint, Plastic Tube
Eyebut Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	36000 lb.
Type	Corrosion-Resistant Anchor
UPC	096359757191

Dimensions

Length	108 in
Rod Diameter	1 in
Weight	91.85 lb

Logistics

Standard Package 1

Product Assets

- [Catalogs - Appendix A - Transmission And Substation Technical Design Manual](#)
- [Installation Manuals - TD06134E_Corrosion_Protected_Disk_Anchors](#)
- [Literature - Anchoring](#)
- [Sales Drawings - Threaded Twineye Rod 1"](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
CH-C2000058AW-SPEC-EN | REV 6/2024