



# Anchor, Disk Rod, 1in X 10ft Twineye

By CHANCE Utility  
Catalog # C2000059AW

Corrosion-Resistant Disk Anchor Protected Rod 1" (25.4 mm) Diameter Rod, 10' (3048 mm) long with Twineye. Cap Nut and fiber washer is attached.



\*Representative Image

### Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading,kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

### Application

Earth Tension Anchoring

### General

Coating	Galvanized, ASTM A-153, Black Paint, Plastic Tube
EyenuT Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	36000 lb.
Type	Corrosion-Resistant Anchor Parts
UPC	096359614753

### Dimensions

Length	120.000 in
Rod Diameter	1.000 in
Weight	50.190 lb

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Appendix A - Transmission And Substation Technical Design Manual \(TD\\_06\\_088\\_E\)](#)  
[Installation Manuals - TD06134E\\_Corrosion\\_Protected\\_Disk\\_Anchors](#)  
[Literature - Anchoring \(CA12002E\)](#)  
[Sales Drawings - Threaded Twineye Rod 1" \(SA2000058AW\)](#)



A proud member of the Hubbell Family.