



Anchor, Disk Rod, 3/4in X 8ft Tripleye

By CHANCE Utility
Catalog # [C2000061AW](#)

Corrosion-Resistant Disk Anchor Protected Rod 0.75" (19.1 mm) Diameter Rod, 8' (2438 mm) long with Tripleye. Cap Nut and fiber washer is attached.



Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

Application

Earth Tension Anchoring

General

| | |
|------------------|--|
| Coating | Galvanized, ASTM A-153, Black Paint, Plastic Tube |
| Eye Nut Style | Tripleye |
| Strength Note | Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. |
| Tensile Strength | 23000 lb. |
| Type | Corrosion-Resistant Anchor Parts |
| UPC | 096359614807 |

Dimensions

| | |
|--------------|-----------|
| Length | 96.000 in |
| Rod Diameter | 0.750 in |
| Weight | 16.550 lb |

Logistics

| | |
|------------------|---|
| Standard Package | 1 |
|------------------|---|

Product Assets

- [Catalogs - Appendix A - Transmission And Substation Technical Design Manual \(TD_06_088_E\)](#)
- [Installation Manuals - TD06134E_Corrosion_Protected_Disk_Anchors](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Threaded Tripleye Rod 3/4" \(SA2000061AW\)](#)



A proud member of the Hubbell Family.