



Rod, Expanding/Cross-Plate Anchor protected tube 3/4in X 9ft Tripleye

By Chance
Catalog # C2000097

Expanding/Cross-Plate Anchor Rod 0.75" (19.1 mm) Diameter Rod, 9' (2743 mm) long with Tripleye with protective plastic tube.

Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading,kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Square nut assembled to rod
- Rods used with Cross-plate and Expanding anchors

Application

Earth Tension Anchoring

General

Catalog Number	C2000097
Coating	Galvanized, ASTM A-153 with Plastic Tube
Eyenum Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load



*Representative Image

Tensile Strength	may significantly lower strength.
Type	23000 lb.
UPC	Anchor Rod 096359647485

Dimensions

Length	108 in
Rod Diameter	0.75 in
Weight	14.043 lb

Logistics

Pallet Quantity	50
Standard Package	3

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06135E_Expanding_Anchors](#)
- [Installation Manuals - TD06136E_Cross_Plate_Anchors](#)
- [Literature - Anchoring](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - C2000097](#)
- [Video - CHANCE Expanding Anchors](#)