



# Anchor, Disk Rod, 1-1/4in X 15ft Tripleye

By CHANCE Utility  
Catalog # [C2000140](#)

Corrosion-Resistant Disk Anchor Protected Rod 1.25" (31.75 mm) Diameter Rod, 15' (4572 mm) long with Tripleye. Cap Nut and fiber washer is attached.



\*Representative Image

## Features

- Thimbleye®, Twineye® and Tripleye® drop forged eye distribute pulling stresses uniformly over individual strands of guy wire and keep the guy wire from spreading, kinking, or bending.
- Hot dipped galvanized per ASTM A153, Black asphalt paint applied over galvanizing, plastic tube assembled on rod
- Includes Fiber Washer and Cap nut
- Rods used with round Disk Anchors

## Application

Earth Tension Anchoring

## General

Coating	Galvanized, ASTM A-153, Black Paint, Plastic Tube
Eye Nut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	58000 lb.
Type	Corrosion-Resistant Anchor Parts
UPC	096359622840

## Dimensions

Length	180.000 in
Rod Diameter	1.250 in
Weight	75 lb

## Logistics

Standard Package	1
------------------	---

## Product Assets

- [Catalogs - Appendix A - Transmission And Substation Technical Design Manual \(TD\\_06\\_088\\_E\)](#)
- [Installation Manuals - TD06134E\\_Corrosion\\_Protected\\_Disk\\_Anchors](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - 30 Inch Diameter Disk Anchor With 15 FT X 1-1/4 Inch 2 Pcs Rod \(SA1022381\)](#)



A proud member of the Hubbell Family.