



T-SLOT CHANNEL TYPE UNDERGROUND CABLE RACK, 30in LENGTH

By CHANCE Utility
Catalog # [C2031126](#)

Cable racking mounts to wall with expansion or anchor bolts for support of cable in underground vault applications. Support hooks (stanchions) and insulator pads complete the installation and are purchased separately.



Features

- 3/16" x 1-1/2 x 9/16" steel channel
- 9/16" dia. mounting holes on 28-1/2" centers
- 18 support hook openings spaced 1-1/2" apart
- Can be overlapped for connecting multiple racks
- Hot dip galvanized per ASTM A-153
- In compliance with ANSI C135.35 standard

General

Coating	Galvanized, ASTM A-153
Material	Steel
Number of Holes	18
UPC	096359013334

Dimensions

Distance From Pole	N/A
Length	30.00 in
Weight	2.74 lb

Logistics

Pallet Quantity	800
-----------------	-----

Product Assets

[Catalogs - Pole Line Hardware](#)
[Sales Drawings - Cable Rack \(SAC2031124\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C2031126-SPEC-EN | REV 7/2023