



## CROSSARM MOUNTED, CUTOUT/ARRESTER BRACKET, 2- 1/2in EXTENSION, NEMA A-TYPE

By CHANCE Utility  
Catalog # [C2060127](#)

Crossarm mounted bracket for mounting a single cutout, arrester or cable terminator.



### Features

- Bracket adjust to fit crossarms from 3" to 4" x 4" to 5"
- Includes one 1/2" x 1-1/2" captive carriage bolt with hex nut, single coil lockwasher and round washer
- Includes back strap and two 3/8" x 5" bolts for crossarm attachment
- L-bracket is 5/16" x 1-1/2" galvanized steel per ASTM A-153

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Type	Crossarm Mounted
UPC	096359014003

### Dimensions

Distance From Pole	N/A
Weight	2.25 lb

### Certifications and Compliance

Industry Standard(s)	NEAM TYPE A
----------------------	-------------

### Logistics

Pallet Quantity	960
-----------------	-----

### Product Assets

[Catalogs - Pole Line Hardware](#)  
[Sales Drawings - NEMA Standard Crossarm Bracket \(SA2060127\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-C2060127-SPEC-EN | REV 7/2023