



## SIDE MOUNT, FLAT BASE, POST-TYPE INSULATOR BRACKET, 8-3/4in POLE OFFSET

By Hubbell  
Catalog # [C2060209](#)

Bracket mounts post-type insulators to side of pole in horizontal position with 30 degree up sweep. Lineman's slang is chicken wing.



### Features

- Mounts to pole with 5/8" dia. through bolt
- Accepts 3/4" dia. insulator line post stud
- Material: 3/8" x 2-1/2' galvanized steel per ASTM A-153

### General

Coating	Galvanized, ASTM A-153
Material	Steel
Style	Flat Back
Type	Bracket
UPC	096359014102

### Dimensions

Distance From Pole	8.75 in
Weight	6.37 lb

### Certifications and Compliance

RUS Listed Reference	eq - Narrow profile brackets & special arm assemblies
----------------------	---

### Logistics

Pallet Quantity	150
-----------------	-----

### Product Assets

[Sales Drawings - Mounting Bracket \(SA16919\)](#)  
[Technical Solutions - CH-C2060209-SPEC-EN](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C2060209-SPEC-EN | REV 1/2024