



CROSSARM INSULATOR PIN with 1in NYLON THREAD, 8in SHAFT LENGTH and 5/8in x 7-1/2in SHANK

By Chance
Catalog # [C2060294P](#)

Insulator pin used to support pin type insulator with 1" NEMA internal thread on crossarm. Refer to sales drawing link for included hardware.



Features

- Minimum thread length of shank is 6"
- Galvanized steel per ASTM A-153

General

Catalog Number	C2060294P
Coating	Galvanized, ASTM A-153
Material	Steel
Type	Pins
UPC	096359568209

Dimensions

Dimensions	15.500 in x 2.987 in x 2.987 in
Distance From Pole	N/A
Height	2.987 in
Length	15.5 in
Length - Threaded Area	6 in
Weight	3.4 lb
Width	2.987 in

Logistics

Carton Quantity	10
Pallet Quantity	480

Product Assets

- [Catalogs - Pole Line Hardware Supplements](#)
- [Installation Manuals - CHANCE® Nylon Thread Insulator Pin Instructions](#)
- [Sales Drawings - Forged Steel Pin](#)