



PLASTIC LASHING STRAP, 27in

By CHANCE Utility
Catalog # [C27PLLC](#)

Lashing straps used in conjunction with spacers to secure communications cable to messenger strand.



Features

- Includes integral buckle for securing
- Loop strength 250 lbs.
- Black acetal with stainless steel locking barbs in buckle
- UV resistant and halogen free
- Use PSC2170130 strap tensioning tool for tensioning and cutting excess strap material

General

Material	Plastic
UPC	096359657088

Dimensions

Length	27 in
Weight	0.05 lb

Logistics

Carton Quantity	500 EA
-----------------	--------

Product Assets

[Sales Drawings - SAC10PLLC](#)
[Video - Hubbell® Messenger Installation \(VI012006E\)](#)

Related Products

[PSC2170130 - TENSIONING TOOL for PLASTIC LASHING STRAPS](#)
[PSC2080426 - STACKABLE SPACER](#)
[CDLC - Lashing Wire Clamp, Type D, 1/4in to 7/16in Strand Size](#)
[PSC2080421 - BELL SPACER CABLE, 1/2in](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-C27PLLC-SPEC-EN | REV 1/2024