



Anchor, Tool, Kelly Bar Adapter, 2.5in Hex, 12,000 ft-lb rating

By CHANCE Utility
Catalog # [C3030936](#)

Anchor, Tool, Kelly Bar Adapter, 2.5in Hex, 12,000 ft-lb rating



*Representative Image

Features

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Kelly bar adapter has twelve holes for 5/8" bolts on a 7-5/8" bolt circle, comes with twelve 5/8" Grade 5 bolts, nuts & lockwashers and bent arm pin with coil lock
- Painted with green paint

Application

Anchor/Pile Installation

General

Bolt Grade	5
Coating	Painted
Kelly Bar Shape	Hex
Number of Bolt Holes	12
Torque Rating	12000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015291

Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Dimensions	8.25 in x 10.500 in x 9.500 in
Height	9.500 in
Kelly Bar Adapter Inside Width	2.5 in
Kelly Bar Hole Distance to Flange	4.25 in
Length	8.25 in
Weight	25.480 lb
Width	10.500 in

Logistics

Pallet Quantity	27
Standard Package	1

Product Assets

- [Catalogs - Anchor Tools \(4A_CA06122E\)](#)
- [Installation Manuals - Instructions for CHANCE Kelly Bar Adapters \(P3031465\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
- [Sales Drawings - Tough One Wrench System \(SA30310008\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

- [C3031223 - Anchor, Tool, Bent Arm Pin, 1/2in X 4.5in](#)
- [PSZ0012553P - Anchor Tool Lockwasher](#)
- [PSZ0012557P - Anchor Tool Bolt](#)
- [PSZ0012552P - Anchor Tool Nut](#)



A proud member of the Hubbell Family.