



## Anchor, Tool, Kelly Bar Adapter, 2.625in Hex, 15,000 ft-lb rating

By CHANCE Utility  
Catalog # [C3030937](#)

Anchor, Tool, Kelly Bar Adapter, 2.625in Hex, 15,000 ft-lb rating



\*Representative Image

### Features

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Kelly bar adapter has twelve holes for 5/8" bolts on a 7-5/8" bolt circle, comes with twelve 5/8" Grade 5 bolts, nuts & lockwashers and bent arm pin with coil lock
- Painted with green paint

### Application

Anchor/Pile Installation

### General

Bolt Grade	5
Coating	Painted
Kelly Bar Shape	Hex
Number of Bolt Holes	12
Torque Rating	15000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015307

### Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Dimensions	8.25 in x 10.500 in x 9.500 in
Height	9.500 in
Kelly Bar Adapter Inside Width	2.625 in
Kelly Bar Hole Distance to Flange	4.25 in
Length	8.25 in
Weight	25.480 lb
Width	10.500 in

### Logistics

Pallet Quantity	36
Standard Package	1

### Product Assets

[Catalogs - Anchor Tools \(4A\\_CA06122E\)](#)  
[Installation Manuals - Instructions for CHANCE Kelly Bar Adapters \(P3031465\)](#)  
[Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)  
[Literature - Anchoring \(CA12002E\)](#)  
[Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)  
[Sales Drawings - Tough One Wrench System \(SA30310008\)](#)  
[Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

### Related Products

[C3031223 - Anchor, Tool, Bent Arm Pin, 1/2in X 4.5in](#)  
[PSZ0012552P - Anchor Tool Nut](#)  
[PSZ0012557P - Anchor Tool Bolt](#)  
[PSZ0012553P - Anchor Tool Lockwasher](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-C3030937-SPEC-EN | REV 1/2024