



Anchor, Tool, Kelly Bar Adapter, 3.0in Hex, 25,000 ft-lb rating

By CHANCE Utility
Catalog # C3030940

Anchor, Tool, Kelly Bar Adapter, 3.0in Hex, 25,000 ft-lb rating



*Representative Image

Features

- Kelly Bar Adapter attaches to truck's torque motor drive shaft (Kelly Bar)
- Kelly bar adapter has twelve holes for 5/8" bolts on a 7-5/8" bolt circle, comes with twelve 5/8" Grade 5 bolts, nuts & lockwashers and bent arm pin with coil lock
- Painted with green paint

Application

Anchor/Pile Installation

General

Bolt Grade	5
Coating	Painted
EU RoHS Indicator	No
Kelly Bar Shape	Hex
Number of Bolt Holes	12
Torque Rating	25000 ft-lbs
Type	Anchor/Pile Installation Tools
UPC	096359015314

Dimensions

Anchor Installation Hole Size	0.625 in
Diameter - Bolt	0.625 in
Diameter - Bolt Circle	7.625 in
Dimensions	8.00 in x 10.500 in x 9.500 in
Height	9.500 in
Kelly Bar Adapter Inside Width	3 in
Kelly Bar Hole Distance to Flange	3.5 in
Length	8.00 in
Weight	31.360 lb
Width	10.500 in

Logistics

Pallet Quantity	48
Standard Package	1

Product Assets

- [Catalogs - Anchor Tools \(4A_CA06122E\)](#)
- [Installation Manuals - Instructions for CHANCE Kelly Bar Adapters \(P3031465\)](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide \(BR06167E\)](#)
- [Sales Drawings - 3"Hex Kelly Bar Adapter \(SA3030940\)](#)
- [Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

Related Products

- [C3031222 - Anchor, Tool, Bent Arm Pin, 5/8in X 5in](#)
- [PSZ0012557P - Anchor Tool Bolt](#)
- [PSZ0012552P - Anchor Tool Nut](#)
- [PSZ0012553P - Anchor Tool Lockwasher](#)



A proud member of the Hubbell Family.