



## Capstan Hoist 1,000 lb. (115V AC) w/ All Purpose Bracket

By: CHANCE Lineman Tools & Equipment  
Catalog # C3080885



Improved design features a multiple-planetary drive/backstop-clutch assembled on the center shaft of a steel gear case with full-length internal teeth. This design handles more rugged jobs, extends service life and reduces maintenance. Lightweight yet powerful, these portable hoists move many heavyweight tasks and can get into remote or difficult-access sites. Examples: Setting utility poles, pulling wheeled equipment over obstacles, raising transformers (even over fences in back lots), hoisting heavy insulators, stringing and tensioning conductors, pulling cable (indoors and underground). Operator effort remains low for typical loads simply by adding wraps on the capstan drum. So little effort is required, any crew member can run the hoist. Control is so accurate, loads can be moved fractions of an inch.

### Features

- 4 wraps of rope = 1:44 ratio. That is, 1 lb. pull on Fall Line develops 44 lb. on Load Line. Therefore, 20 lb. of pull develops 880 lb. of lift.

### General

EU RoHS Indicator	No
Power Supply	115V AC
Rope Speed at Rated Load	40' (12 m) per minute
Strength Rating - Ultimate	1000 lb
Style	Capstan Hoist Kit
UPC	096359015857

### Dimensions

Weight	59 lb
WeightMetric	26.761949830000002 kg

### Logistics

Standard Package	1
------------------	---

### Product Assets

[Catalogs - Powered Hoists \(1150\)](#)

[Owner's Manuals - CHANCE® Series 90 Capstan Hoist](#)



A proud member of the Hubbell Family.