



3/4 Ton Ratchet Roller Chain Hoist

By CHANCE Utility
Catalog # [C3090457](#)

Roller-style (bicycle) chain offers an alternative in two of the same load ratings from the CHANCE link-style chain hoist line.



Features

- All working parts fully enclosed in housing
- Polished high-strength alloy steel chain
- Forged steel 360° swivelling load hooks with spring-loaded latches
- Controls automatically lock when under load
- Ratchet handle swings to either side
- Lifetime oil-impregnated bronze sleeve bearings require no additional lubrication

General

Application - For Use On	65.0 lb., 29.5 kg
Connector	13 in, 33.0 cm
Strength Rating - Ultimate	1500 lb
Style	Roller Chain Hoist
UPC	096359016298

Dimensions

Dimensions	20 in x 4.5 in x 4.75 in
Height	4.75 in
Length	20 in
LengthMetric	50.8 mm
Weight	12.5 lb
WeightMetric	5.7 kg
Width	4.5 in

Logistics

Pallet Quantity	48
Standard Package	1

Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)
[Installation Manuals - CHANCE ¾-Ton Chain Hoist Instruction Manual \(P309-0431\)](#)
[Literature - Tips of the Trade - Hoist Safety \(BR09004E\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C3090457-SPEC-EN | REV 8/2023