

## Grip-All 6 ft (1.8 m)

By CHANCE Lineman Grade Tools  
Catalog # [C4030292](#)



The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole.

### Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control "finger" on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or "shotgun") incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas® pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

### Specifications

EU RoHS Indicator No

### Dimensions

|                                    |                           |
|------------------------------------|---------------------------|
| WeightMetric                       | 4.4 kg                    |
| WidthMetric                        | 111 mm                    |
| Dimension - L Length Overall<br>mm | 2.0 m                     |
| Dimension - Length Overall<br>inch | 78 in                     |
| HeightMetric                       | 111 mm                    |
| Length Metric                      | 2134 mm                   |
| Width                              | 4.38 in                   |
| Weight                             | 9.8 lb.                   |
| Height                             | 4.38 in                   |
| Length                             | 84 in                     |
| Dimensions Metric                  | 2134 mm x 111 mm x 111 mm |
| Dimensions                         | 84 in x 4.38 in x 4.38 in |

### General

|                       |  |
|-----------------------|--|
| Storage Bag Included? | P643-6 (Bag not included. Must be ordered separately.) |
| UPC                   | 096359018063   |
| Style                 | Standard   |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

### Product Assets

[Catalog \[English\]](#)  
[Installation Manual \[English\]](#)