



Grip-All, 12'

By: CHANCE Lineman Tools & Equipment
Catalog # [C4030295](#)



GRIPALL - 12FT 7IN, The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole. Although primarily designed for installing hot-line and grounding clamps, it serves both overhead and underground circuits with various end fittings. Commonly called a "shotgun," the operating mechanism incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into the tool head. A thumb latch then must be depressed to release the locked hand grip so it can open the hook. While the tool head is of Lexan® for close-quarter operations, the worker must maintain recommended working distance solely on the Epoxiglas™ pole section of the handle as the hook and its actuator are metal parts. Easy to care for, Grip-All sticks do not require field stripping to clean. All insulated parts including the operating rod are outside the main pole, readily accessible to wipe dry. CAUTION: Do not clean the plastic head with solvent.

*Representative Image

Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control "finger" on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or "shotgun") incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas™ pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

Dimensions

Dimensions	155 in x 4.38 in x 4.38 in
Height	4.38 in
Length	155 in
LengthMetric	393.7 mm
Weight	15.9 lb
WeightMetric	7.2 kg
Width	4.38 in

Product Assets

[Catalogs - Insulated Hand Tools \(2100\)](#)
[Installation Manuals - CHANCE® Tools Manuals \(CENT_LTE_IOM_EN_00158\)](#)<LineBreak/>
[Sales Drawings - Epoxiglas Gripall \(SA4030291\)](#)

Related Products

[P4032312P - Heavy Duty End Cap for 1-1/4" Epoxiglas Pole](#)

General

EU RoHS Indicator	No
Storage Bag Included?	P643-12 (Bag not included. Must be ordered separately.)
Style	Standard
UPC	096359018148



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C4030295-SPEC-EN | REV 4/2023