



Grip-All Hinged 6 ft (1.8 m)

By CHANCE Lineman Grade Tools
Catalog # [C4030296](#)

The 6' Hinged Grip-All with Universal Head extends to 6'9", and folds to 3'4". The Grip-All is the most versatile tool in a lineworker's hands. The Grip-All stick puts an easy-to-control "finger" on an insulated pole.

Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control "finger" on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or "shotgun") incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas® pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

Dimensions



| | |
|------------------------------------|---------------------------|
| WeightMetric | 3.6 kg |
| WidthMetric | 184 mm |
| Dimension - L Length Overall mm | 1.4 m |
| Dimension - Length Overall inch | 77 in |
| HeightMetric | 184 mm |
| Length Metric | 1981 mm |
| Width | 7.25 in |
| Weight | 8.0 lb. |
| Height | 7.25 in |
| Length | 78 in |
| Dimensions Metric | 1981 mm x 184 mm x 184 mm |
| Dimensions | 78 in x 7.25 in x 7.25 in |

General

| | |
|-----------------------|--|
| Storage Bag Included? | P643-2 (Bag not included. Must be ordered separately.) |
| UPC | 096359018155 |
| Style | Hinged |

Logistics

| | |
|-----------------|----|
| Pallet Quantity | 40 |
|-----------------|----|

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)