



Grip-All Hinged 14 ft (4.2 m) (4.2 m)

By CHANCE Lineman Grade Tools
Catalog # [C4030342](#)

The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole.



Features

- External Operating Rod Type
- Tested per OSHA & ASTM F711
- Versatile tool puts an easy-to-control "finger" on an insulated pole
- Primarily designed for installing hot-line and grounding clamps
- Also serves both overhead and underground circuits with various end fittings
- Operating mechanism (or "shotgun") incorporates a sliding hand grip that opens the hook to grasp a clamp eyescrew and retract it into tool head
- Latch must be depressed to release locked hand grip that opens the hook
- For smooth operation, investment-cast stainless-steel components include Jaw, Jaw Holder, Safety Stop, Lockbar and Latch
- Lexan® tool head is designed for close-quarter operations
- Worker must maintain recommended work distance based solely on the Epoxiglas® pole section of the handle, as the hook and its actuator are metal parts
- Easy-care Grip-All Clampsticks do not require field stripping to clean
- All insulated parts, including the operating rod, are outside the main pole, readily accessible to wipe dry

Specifications

EU RoHS Indicator No

Dimensions

WeightMetric	6.4 kg
WidthMetric	184 mm
Dimension - L Length Overall mm	4.4 m
Dimension - Length Overall inch	176 in
HeightMetric	184 mm
Length Metric	4420 mm
Width	7.25 in
Weight	14.0 lb.
Height	7.25 in
Length	174 in
Dimensions Metric	4420 mm x 184 mm x 184 mm
Dimensions	174 in x 7.25 in x 7.25 in

General

UPC 096359018278
Style Hinged

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[English\]](#)