



Grip-All Telescoping 5 ft 7 in to 8 ft (1.7 m to 2.4 m)

By CHANCE Lineman Grade Tools
Catalog # [C4031035](#)

The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole.



Features

- Tested per OSHA & ASTM F711
- Available in two sizes, each readily locks at variable working lengths
- Design features rotating coupler and an engineered positive-lock button with safety stop to keep sections from parting or hook releasing while in use
- Mechanism locks sections into a solid, rattle-free tool
- Black head makes it obvious head is not included in minimum approach distance
- Can replace several conventional clampsticks
- Allows linemen to adhere to safe-working distances and positioning needs, with fewer sticks
- Reduces the number of clampsticks required on a line truck, saving limited storage space
- Engineered interface between sections ensure tool retracts with full control
- Close fit helps keep out dirt and moisture
- Top section is made with foam-center Epoxiglas® insulated pole
- Functions of this telescoping style are identical to fixed-length style
- All controls can be easily accessed while wearing gloves
- Easy to disassemble, stick must be kept clean and dry inside to ensure long life
- T4031245 Button and Spring Replacement Kit

Specifications

EU RoHS Indicator No

Dimensions

WeightMetric	4.5 kg
WidthMetric	111 mm
Length - Retracted Metric	1.5 m
Length - Retracted	67 in
HeightMetric	111 mm
Length Metric	2438 mm
Width	4.38 in
Weight	10.0 lb.
Height	4.38 in
Length	96 in
Dimensions Metric	2438 mm x 111 mm x 111 mm
Dimensions	96 in x 4.38 in x 4.38 in

General

Storage Bag Included?	P643-6 (Bag not included. Must be ordered separately.)
UPC	096359018841
Style	Telescoping

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)