



Grip-All Telescoping 8 ft 7 in to 14 ft (2.5 m to 4.2 m)

By CHANCE Lineman Grade Tools
Catalog # [C4031036](#)

The most versatile tool in a lineworker's hands, the Grip-All stick puts an easy-to-control "finger" on an insulated pole.



Features

- Tested per OSHA & ASTM F711
- Available in two sizes, each readily locks at variable working lengths
- Design features rotating coupler and an engineered positive-lock button with safety stop to keep sections from parting or hook releasing while in use
- Mechanism locks sections into a solid, rattle-free tool
- Black head makes it obvious head is not included in minimum approach distance
- Can replace several conventional clampsticks
- Allows linemen to adhere to safe-working distances and positioning needs, with fewer sticks
- Reduces the number of clampsticks required on a line truck, saving limited storage space
- Engineered interface between sections ensure tool retracts with full control
- Close fit helps keep out dirt and moisture
- Top section is made with foam-center Epoxiglas® insulated pole
- Functions of this telescoping style are identical to fixed-length style
- All controls can be easily accessed while wearing gloves
- Easy to disassemble, stick must be kept clean and dry inside to ensure long life
- T4031245 Button and Spring Replacement Kit

Specifications

EU RoHS Indicator No

Dimensions

WeightMetric	6.8 kg
WidthMetric	114 mm
Length - Retracted Metric	2.5 m
Length - Retracted	103 in
HeightMetric	114 mm
Length Metric	4267 mm
Width	4.5 in
Weight	15 lb.
Height	4.5 in
Length	168 in
Dimensions Metric	4267 mm x 114 mm x 114 mm
Dimensions	168 in x 4.5 in x 4.5 in

General

Storage Bag Included?	P643-8 (Bag not included. Must be ordered separately.)
UPC	096359018858
Style	Telescoping

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)