



CHANCE® 12FT LOAD-PICK TOOL SET 1/0 15KV, ORANGE JUMPER HANDLE

By: CHANCE Lineman Tools & Equipment
Catalog # [C4031560](#)



CHANCE® 12FT LOAD-PICK TOOL SET 1/0 15KV, ORANGE JUMPER HANDLE

Features

- Rated to pickup and carry up to 250 amp loads at 15kV
- Includes Load-Pickup Device, Orange Jumper Clamp, and 12ft of 1/0 15kV Jumper Cable
- Load-Pickup Tool and Jumper Clamp fit conductors from #6 Copper (0.162") through 795 ACSR (1.108")
- Clean and inspect Load-Pickup Tool head after every 25 operations or at least once every 90 days
- Adequate rubber gloves must be worn when using this equipment
- Orange-tinted translucent Lexan® housing permits easy visual inspection of the Load-Pickup head

General

Style Complete Set
UPC 096359019176

Dimensions

Length 12 ft
Weight 22.54 lb

Electrical Ratings

Amperage Rating	250
Current Rating	250 A
Voltage - Maximum	15 kV

Conductor Related

Conductor Diameter (Main) - Maximum	1.108 in
Conductor Diameter (Main) - Minimum	0.162 in
Conductor Size	1/0 AWG

Logistics

Pallet Quantity	32
-----------------	----

Product Assets

[Catalogs - Jumpers & Load Pickup Tools \(2300\)](#)
[Sales Drawings - SA_C4031631_LOAD_PICK_UP_TOOL](#)
[Video - Chance Load Pick-Up Maintenance \(VI09077E0920\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-C4031560-SPEC-EN | REV 4/2023